

Dane techniczne dla produktu: NLKWIC433S

Emerg.lum. KWI clear Autotest 4x1W ERT-LED 3h 230V AC ceil.

With exchangeable lenses, corridor lenses in scope of delivery included, 1h/3h/8h adjustable, ceiling surface mounting, security luminaire with transparent cover for illumination of escape routes, viewing distance: 16m, IP65, IK06, protection class II, 1h: 520lm; 3h: 520lm; 8h: 210lm, LiFePO4 battery




Dane techniczne

Długość (mm)	390,00
Szerokość (mm)	93,00
Wysokość (mm)	99,00
Waga (kg)	0,70
Rodzaj oprawy oświetleniowej	awaryjna
EB-ZB	Oprawy autonomiczne
Funkcja	autotest
Wersja	oprawy plastikowe
Design / Seria	KWI
Bezhalogenowy	obudowa wykonana z tworzywa sztucznego bezhalogenowego
Kolor	RAL 9003

Dane techniczne - kontynuacja

Widoczność (mb)	16
Źródło światła	ERT-LED (4W)
Strumień świetlny	1h: 520;3h: 520;8h: 210
Zakres napięcia (V)	230V AC 50Hz ±20%
Power maintained mode (W)	7
Power non-maintained mode (W)	2
Power max. (W)	8,20
Akumulatory (V/Ah)	2x 3,2V/3,3Ah LiFePO4
Stopień szczelności	IP65
Odporność na uderzenia	IK06
Montaż	sufitowy natynkowy
Min. temperatura otoczenia (°C)	-5
Maks. temperatura otoczenia (°C)	40
AA klasa E 8101	AA4
Producent	Schrack

Dimensions (mm)



Spacing table - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 1h/3h

					
2,00	4,14	10,15	9,84	9,45	3,79
2,50	4,46	11,2	10,77	10,21	4,14
3,00	4,73	12,01	11,52	10,97	4,47
3,50	4,94	12,63	12,15	11,68	4,67
4,00	5,05	13,18	12,77	12,36	4,79
5,00	5,36	14,04	13,66	13,28	4,89
6,00	4,7	14,45	14,12	13,72	4,72
7,00	4,34	14,61	14,29	13,9	4,03
8,00	3,7	14,8	13,71	13,63	3,54
9,00	2,17	13,05	12,97	12,89	2,24

Spacing table with corridor lenses (included in scope delivery) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	7,36	17,11	12,52	7,88	3,09
2,50	8,47	19,63	14,05	8,45	3,28
3,00	9,46	21,93	15,41	8,95	3,39
3,50	10,37	24,15	16,69	9,32	3,43
4,00	11,2	26,19	17,85	9,58	3,45
5,00	4,73	24,45	13,86	9,8	3,38
6,00	5,23	23,48	11,64	9,82	3,17
7,00	2,93	13,48	11,45	9,69	2,58

Spacing table with round lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	4,37	9,66	9,50 9,29 4,19	4,89	1,89
2,50	5,14	11,36	11,13 10,84 4,98	6,12	2,36
3,00	5,86	12,86	12,66 12,46 5,68	7,34	2,83
3,50	6,51	14,46	14,24 14,01 6,31	8,57	3,3
4,00	7,1	15,94	15,69 15,44 6,80	9,79	3,78
5,00	4,53	18,43	16,35 17,85 5,61	10,53	4,04
6,00	0,96	15,82	15,42 15,08 1,07	11,02	4,18

Spacing table with spot lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	1,84	4,46	4,46	4,46	1,84
2,50	2,3	5,58	5,58	5,58	2,3
3,00	2,77	6,7	6,7	6,7	2,77
3,50	3,08	7,33	7,33	7,33	3,08
4,00	3,3	7,75	7,75	7,75	3,3
5,00	3,84	8,81	8,81	8,81	3,84
6,00	4,26	9,8	9,8	9,8	4,26
7,00	4,65	10,85	10,85	10,85	4,65
8,00	4,97	11,74	11,74	11,74	4,97
9,00	5,21	12,49	12,49	12,49	5,21
10,00	5,35	13,27	13,27	13,27	5,35
12,00	5,4	14,46	14,46	14,46	5,4
14,00	5,18	15,16	15,16	15,16	5,18
16,00	4,69	15,36	15,36	15,36	4,69

Spacing table with high corridor lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	4,54	10,47	7,67	4,83	1,79
2,50	5,65	13,09	9,59	6,03	2,24
3,00	6,28	14,77	10,84	6,83	2,47
3,50	6,81	16,21	11,6	6,99	2,45
4,00	7,29	17,52	12,28	7,06	2,35
5,00	8,1	19,73	13,35	6,98	1,91
6,00	8,75	21,58	13,68	6,07	2
7,00	9,11	23,16	14,24	5,46	2,12
8,00	9,33	24,52	14,54	5,55	2,16
9,00	9,51	25,69	14,72	5,88	2,23
10,00	9,27	26,29	14,82	6,08	2,29
12,00	8,41	27,15	14,19	6,24	2,22
14,00	7,09	26,85	13,73	6,51	1,92
16,00	4,53	24,91	12,22	6,48	1,36

Spacing table with corridor lenses (included in scope delivery) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	6,01	14,07	9,87	5,72	2,13
2,50	6,86	16,17	11,05	6,02	2,15
3,00	2,82	14,58	9,53	6,15	2,12
3,50	3,1	16,11	7,43	6,19	2,05
4,00	3,32	7,87	7,07	6,16	1,93

Spacing table (without lenses) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80 - Autonomy time 8h

					
2,00	3,03	7,71	7,44	7,1	2,87
2,50	3,17	8,29	8,05	7,8	3,01
3,00	3,21	8,77	8,55	8,3	3,08
3,50	3,22	9,04	8,8	8,57	3,05
4,00	2,94	9,24	9,01	8,73	2,9
5,00	2,37	9,39	8,74	8,66	2,23
6,00	0,43	8,09	7,86	7,86	0,44

Spacing table with round lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	3,83	8,46	8,32	8,19	3,72
2,50	4,45	9,98	9,83	9,68	4,32
3,00	2,8	11,34	11,17	10,99	4,2
3,50	1,85	10,42	10,25	10,04	1,64

Spacing table with spot lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	1,8	4,46	4,46	4,46	1,8
2,50	2,03	4,81	4,81	4,81	2,03
3,00	2,32	5,38	5,38	5,38	2,32
3,50	2,56	5,82	5,82	5,82	2,56
4,00	2,75	6,39	6,39	6,39	2,75
5,00	3,11	7,35	7,35	7,35	3,11
6,00	3,33	8,13	8,13	8,13	3,33
7,00	3,42	8,82	8,82	8,82	3,42
8,00	3,39	9,32	9,32	9,32	3,39
9,00	3,25	9,62	9,62	9,62	3,25
10,00	3,01	9,73	9,73	9,73	3,01
7,00	3,42	8,82	8,82	8,82	3,42
9,00	3,25	9,62	9,62	9,62	3,25
11,00	2,61	9,69	9,69	9,69	2,61

Spacing table with high corridor lenses (must be ordered separately) - Min. illuminance on the center line +/- 0.5 m: 1 lx - Maintenance factor 0.80

					
2,00	3,91	9,4	6,88	4,32	1,51
2,50	4,41	10,74	7,57	4,42	1,42
3,00	4,83	11,86	8,11	4,42	1,22
3,50	5,18	12,84	8,51	4,13	1,23
4,00	5,43	13,7	8,63	3,49	1,29
5,00	5,69	15,15	8,97	3,44	1,38
6,00	5,71	16,1	9,15	3,75	1,42
7,00	5,29	16,58	9,09	3,88	1,44
8,00	4,83	16,94	8,79	3,98	1,36
9,00	4,03	16,43	8,31	4,1	1,19
10,00	2,72	15,47	7,54	4,08	0,9

Lista produktów

OPIS	Nr katalogowy
Emerg.lum. KWI clear Autotest 4x1W ERT-LED 3h 230V AC ceil. With exchangeable lenses, corridor lenses in scope of delivery included, 1h/3h/8h adjustable, ceiling surface mounting, security luminaire with transparent cover for illumination of escape routes, viewing distance: 16m, IP65, IK06, protection class II, 1h: 520lm; 3h: 520lm; 8h: 210lm, LiFePO4 battery	NLKWIC433S
Dodatkowe akcesoria	
Ball protection gasket for KW and C1	NLBKW
Pictogram set for NLKWI.. left, right, up, down	NLKWIPIKTO
Zawiesie 500 mm, kolor biały, okablowane	NL2PW
Wall bracket white suitable for: KB, KX, KW, KCD, KE, GX, RX	NLAWX001
Set 2 accus LiFePO4 3,2V 3,3Ah f. luminaires. w. LEO or LPK LiFePO4 - Lithium-iron phosphate battery, UN3480 - UN 3480 : Lithium-Ion batteries	NLAKKU323L
4 LED changeable lenses: Corridor-illuminating escape routes Suitable for emergency luminaires with exchangeable lens system	NLLSYSF4
4 LED changeable lens: Round-illuminating circular surfaces Suitable for emergency luminaires with changeable lens system	NLLSYSR4
4 LED changeable lens: Spot area illumination for high rooms Suitable for emergency luminaires with changeable lens system	NLLSYSS4
4 LED changeable lens: Beam-asymmetric illumination For illumination of safety equipment (e.g. first aid boxes, fire extinguishers, etc.), Suitable for emergency luminaires with changeable lens system	NLLSYSB4
	NLTESTSC2
Protective cover for test buttons NLTEST2---	NLTEST2COV